

Product Description: Stat-Rite® S680 is a static dissipative **PETG** alloy. Stat-Rite S680 utilizes the patented Stat-Rite inherently dissipative polymer (IDP) alloy system to provide clean, permanent ESD protection. Stat-Rite® IDP alloys provide consistent static dissipation even when extruded, injection molded or thermoformed into components.

Properties (typical)	S680	Units	Test Method
Host Polymer	PETG		
Filler	IDP Alloy		
Color	Light Blue		
Specific Gravity	1.25	g/cc	ASTM D-792
Electrical Properties:			
Surface Resistivity	2 x 10 ⁹	Ω/square	ASTM D-257 (50% R.H.)
Surface Resistance	8 x 10 ⁸	Ω	ESD S11.11 (12% R.H.)
Volume Resistivity	2 x 10 ⁹	Ω-cm	ASTM D-257
Static Decay Rate			
+5000 V to 50 V	0.01	Seconds	FTMS-101C (12% R.H.)
-5000 V to -50 V	0.01		
+1000 V to 100 V	0.1	Seconds	Charged Plate Monitor (50% R.H.)
Tribocharge (Nitrile Glove)	10	Volts	Lubrizol Advanced Materials Test Method
Mechanical Properties:			
Tensile Strength @ Break	4100 (28)	psi (MPa)	ASTM D-638
Tensile Elongation, Break	350	%	ASTM D-638
Tensile Modulus	160,000 (1240)	psi (MPa)	ASTM D-638
Flexural Modulus	180,000 (1240)	psi (MPa)	ASTM D-790-92
HDT @ 66 psi	140 (60)	°F (°C)	ASTM D-648
HDT @ 264 psi	131 (55)		
Notched Izod Impact	18 (942)	ft-lb / in (J/m)	ASTM D-256-92
These are typical values and should not be used for establishing product specifications. Contact Lubrizol Advanced Materials, Inc if you need data for this purpose.			

- Stat-Rite® S680 is available in sheet or pellet form.

FEATURES

- Permanent static dissipative
- Humidity insensitive
- Ultra-clean: low off-gassing, low ionic contamination
- Colorable
- Durable: Can be used for years and years

APPLICATIONS

- Medical device packaging
- Electronic component handling
- Hard disk packaging

June 4, 2007

The information contained herein is believed to be reliable, but no representations, guarantees or warranties of any kind are made as to its accuracy, suitability for particular applications or the results to be obtained. The information is based on laboratory work with small-scale equipment and does not necessarily indicate end product performance. Because of the variations in methods, conditions and equipment used commercially in processing these materials, no warranties or guarantees are made as to the suitability of the products for the applications disclosed. Full-scale testing and end product performance are the responsibility of the user. Lubrizol Advanced Materials, Inc. shall not be liable for and the customer assumes all risk and liability of any use or handling of any material beyond Lubrizol Advanced Materials, Inc.'s direct control. THE SELLER MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Nothing contained herein is to be considered as permission, recommendation, nor as an inducement to practice any patented invention without permission of the patent owner.

Lubrizol Advanced Materials, Inc.
 9911 Brecksville Road
 Cleveland, OH 44141-3247
 800-380-5397
www.stat-rite.com

HANDLING CONSIDERATIONS

Properties of all Stat-Rite® polymer products in the molten state are adversely affected by moisture. Although Stat-Rite products are dry when packaged, trace amounts of moisture can be absorbed during storage and handling. For best results, always keep this material in unopened factory packaging until use.

PRODUCT DESCRIPTION

Stat-Rite S680 is a static dissipative *PETG* alloy. **Stat-Rite S680** utilizes the patented Stat-Rite inherently dissipative polymer (IDP) alloy system to provide clean, permanent ESD protection. Stat-Rite® IDP alloys provide consistent static dissipation even when extruded, injection molded and thermoformed into components.

Typical Cleanliness Properties:

Cleanroom Properties	Test Method	Test Results
Outgassing Components:	Lubrizol Advanced Materials Test Method: #3010-3	µg/g
Total Organics		3.0
MMA		0.1
Styrene		<0.02
Toluene		<0.02
Ionic Content – Anions	Lubrizol Advanced Materials Test Method #3010-4	ng/cm ²
F-		<2.5
Cl-		3
NO ₃ ⁻		<0.5
SO ₄ ⁻		<0.6
PO ₄ ⁻		2
Non-Volatile Residue	Lubrizol Advanced Materials Test Method #3010-5	µg/cm ² 1.1